

ALPA Review - Stitch 6x - Phase One IQ250

LCC Correction




image circle 55 mm
sensor 33x44 mm

image circle 70 mm

image circle 80 mm


image circle 90 mm

image circle 108 mm

ALPA 12 MAX - IQ250 - Rodenstock/ALPA HR Alpagon 4.0/32 mm
6x stitch, back in portrait orientation (beyond official image circle of 90 mm)
1st row rise 10 mm, shift left/right 18 mm
2nd row rise 20 mm, shift left/right 18 mm

ALPA Review - Stitch 6x - Phase One IQ250

Before LCC Correction



ALPA 12 MAX - IQ250 - Rodenstock/ALPA HR Alpagon 4.0/32 mm
6x stitch, back in portrait orientation (beyond official image circle of 90 mm)
1st row rise 10 mm, shift left/right 18 mm
2nd row rise 20 mm, shift left/right 18 mm